Value Proposition Densito & Densito Pro

Density2Go

Simple Operation		Chemical	F&B	MPE	Pharma
Redefine the way you measure	Analyze on the go : with an ergonomic design and light weight, the instrument fits nicely into your hand for lab or field use — and takes up minimal space on the bench	•	•	•	•
	Measure comfortably using the joystick to control the automatic sampling pump , and avoid the added strain of manual sampling	•	•	•	•
	Guide operators through entire measurement and cleaning cycles using the built-in guided workflow option	•	•	•	•
	Understand exactly what you need to do with straightforward onscreen directions in twelve different languages	•	•	•	•
afe Results					
Trust your results	Obtain quick measurement results with an accuracy up to the third decimal place	•	•	•	•
	Set up a range of acceptable limits for your product: results outside this range are color-coded for instant identification	•	•	•	•
	Ensure accurate and reliable measurements, reduce unexpected downtime, and extend the lifetime of your device with regular maintenance and calibration provided by Mettler-Toledo Service	•	•	•	•
Manage your data	Simply point and shoot to enter sample IDs using the built-in RFID and barcode reader*	•	•	•	•
	Print your results directly after the experiment using a USB or portable Bluetooth printer	•	•	•	•
	Fully manage your data and create graphs with EasyDirect PC software	•	•	•	•
Sustainable Value					
Suitable for all industries	Work any way you want: with or without its protective cover, the instrument is suited for different, rugged environments	•	•	•	•
	The sky is the limit: whether laboratory or field, use the instrument in a variety of industries , from chemical to F&B and more	•	•	•	•

^{*}Available with DensitoPro only

Very relevant;Relevant;Less relevant